



■ Standard

H	T	P g6	Artikelnummer		L Auswahl											
			Ausführung	P												
2.5	1.2	-0.002 -0.008	D-EPN	1	100	125	160	200								
				1.1	100	125	160	200								
				1.2	100	125	160	200								
3	1.5	-0.002 -0.008	D-EPN	1.5	100	125	160	200	250							
				1.8	100	125	160	200								
4	2	-0.002 -0.008	D-EPN	2	100	125	160	200	250	315						
5				100	125	160	200	250	315	400						
6	3	-0.004 -0.012	D-EPN	3	100	125	160	200	250	315	400	500				
7				100	125	160	200	250	315	400						
8	3	-0.004 -0.012	D-EPN	4	100	125	160	200	250	315	400	500	630			
10				100	125	160	200	250	315	400	500	630	800	1000		
12	5	-0.005 -0.014	D-EPN	5	100	125	160	200	250	315	400	500	630	800	1000	
				5.5	100	125	160	200	250	315	400	500				
14	5	-0.005 -0.014	D-EPN	6	100	125	160	200	250	315	400	500	630	800	1000	
				6.5	100	125	160	200	250	315	400	500				
16	7	-0.006 -0.017	D-EPN	7	100	125	160	200	250	315	400	500				
				7.5	100	125	160	200	250	315	400	500				
18	7	-0.006 -0.017	D-EPN	8	100	125	160	200	250	315	400	500	630	800	1000	
				8.5	100	125	160	200	250	315	400	500				
22	7	-0.006 -0.017	D-EPN	9	100	125	160	200	250	315	400	500	630			
				9.5	100	125	160	200	250	315	400	500				
24	7	-0.006 -0.017	D-EPN	10	100	125	160	200	250	315	400	500	630	800	1000	
				10.5	100	125	160	200	250	315	400	500				
26	8	-0.007 -0.020	D-EPN	11	100	125	160	200	250	315	400	500				
				12	100	125	160	200	250	315	400	500	630	800	1000	
28	8	-0.007 -0.020	D-EPN	12.2	125	160	200	250	315	400	500	630				
				12.5	100	125	160	200	250	315	400	500				
32	10	-0.007 -0.020	D-EPN	14	100	125	160	200	250	315	400	500	630			
				16	100	125	160	200	250	315	400	500	630	800	1000	
32	10	-0.007 -0.020	D-EPN	18	125	160	200	250	315	400	500	630	800	1000		
				20	100	125	160	200	250	315	400	500	630	800	1000	
32	10	-0.007 -0.020	D-EPN	25	125	160	200	250	315	400	500	630				

Bestellung **D-EPN 3 - 100**

■ L Abmessungen auswählen

H	T	P g6	Artikelnummer		L Schritte
			Ausführung	P	
2.5	1.2	-0.002	D-EPN-L	1	40.00 ~ 200.00
				1.5	40.00 ~ 200.00
4	2	-0.008	D-EPN-L	2	40.00 ~ 315.00
				2.5	40.00 ~ 315.00
6	3	-0.004	D-EPN-L	3	40.00 ~ 400.00
				3.5	40.00 ~ 400.00
8	3	-0.004	D-EPN-L	4	40.00 ~ 500.00
				4.5	40.00 ~ 250.00
10	3	-0.012	D-EPN-L	5	40.00 ~ 400.00
				5.5	40.00 ~ 200.00
12	5	-0.005	D-EPN-L	6	40.00 ~ 1000.00
				6.5	100.00 ~ 250.00
14	5	-0.014	D-EPN-L	8	
				10	
18	7	-0.006	D-EPN-L	12	100.00 ~ 1000.00
				16	
26	8	-0.007	D-EPN-L	20	
				25	100.00 ~ 500.00

Option **Artikelnummer** - **L** - **P** - (KC · WKC · usw.)
D-EPNB 4.5 - 248.35 - P4.23 - WKC2.115

Option	Code	Spezifikation
	KC	Einfache Verdrehssicherung P/2 ≤ KC < H/2 (1) Zum Ausrichten der Nut auf dem Schaftdurchmesser Einheit der Auswahl 0.005-mm-Schritte möglich
	WKC	Doppelte Verdrehssicherung P/2 ≤ WKC < H/2 (2) Auswahl frei positionierbarer Flächen Einheit der Auswahl 0.1mm

■ L · P Abmessung auswählen

H	T	P g6	Artikelnummer		L Schritte	P Schritte
			Ausführung	No.		
2.5	1.2	-0.002	D-EPNB	1	40.00 ~ 200.00	0.50 ~ 1.00
				1.5	40.00 ~ 200.00	1.01 ~ 1.50
4	2	-0.008	D-EPNB	2	40.00 ~ 315.00	1.51 ~ 2.00
				2.5	40.00 ~ 315.00	2.01 ~ 2.50
6	3	-0.004	D-EPNB	3	40.00 ~ 400.00	2.51 ~ 3.00
				3.5	40.00 ~ 400.00	3.01 ~ 3.50
8	3	-0.004	D-EPNB	4	40.00 ~ 500.00	3.51 ~ 4.00
				4.5	40.00 ~ 250.00	4.01 ~ 4.50
10	3	-0.012	D-EPNB	5	40.00 ~ 400.00	4.51 ~ 5.00
				5.5	40.00 ~ 200.00	5.01 ~ 5.50
12	5	-0.005	D-EPNB	6	40.00 ~ 1000.00	5.51 ~ 6.00
				6.5	100.00 ~ 250.00	6.01 ~ 6.50
14	5	-0.014	D-EPNB	8		6.51 ~ 8.00
				10		8.01 ~ 10.00
18	7	-0.006	D-EPNB	12	100.00 ~ 1000.00	10.01 ~ 12.00
				16		12.01 ~ 16.00
26	8	-0.007	D-EPNB	20		16.01 ~ 20.00
				25	100.00 ~ 500.00	20.01 ~ 25.00

Einzelheiten zur Änderung **P.4**

Option	Code	Spezifikation
	HC	HC=0.1-mm-Schritten P+1 ≤ HC < H, P ≥ 1.5

Bestellung **Artikelnummer** - **L** - **P**
D-EPN-L 1 - 100.00
D-EPNB 1 - 100.00 - P0.50