


Leiterquerschnitt / wire gauge: 4mm² / AWG 12
 Abisolierlänge / stripping length: 9,5mm



All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Masse / Free size tolerances		
				Dat.	Name	Massstab / Scale 5:1	Han C Buchsenkontakt, gedreht 40A Han C female contact, turned 40A versilbert / silver plated	
			Detail.	20.12.05	Ho			
			Insp.		SP			
413759	19.03.08	Rull	Stand.					
412400	29.08.06	ML	HARTING Electric GmbH & Co. KG				TB 09 32 000 6207	
411928			D-32339 Espelkamp					
Mod.	Dat.	Name					Sub. TB 09 32 000 620. v. 18.06.99	
							Blatt / page	