

SAI M23 CRIMPING TOOL 2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Weidmüller bietet für den Bereich der Sensor-Aktor Verkabelung unterschiedlichstes Werkzeug und Zubehör an.

Allgemeine Bestelldaten

Ausführung	Crimpwerkzeug für Signalkontakte
Best.-Nr.	1203960000
Typ	SAI M23 CRIMPING TOOL 2
GTIN (EAN)	4050118000764
VPE	1 Stück

Erstellungs-Datum 21. Februar 2023 19:03:19 MEZ

Katalogstand 18.02.2023 / Technische Änderungen vorbehalten

SAI M23 CRIMPING TOOL 2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Abmessungen und Gewichte

Nettogewicht 478 g

Temperaturen

Betriebstemperatur, min. -40 °C Betriebstemperatur, max. 125 °C

Klassifikationen

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Umweltanforderungen

REACH SVHC Lead 7439-92-1
 SCIP 7baf363e-d867-435e-844e-c01f32ebf146

Zulassungen

Zulassungen



Downloads

Kataloge [Catalogues in PDF-format](#)
 Broschüren [FL FIELDWIRING EN](#)
[FL FIELDWIRING EN](#)

Crimping settings

Adjustment mechanism to set the crimping and locator position

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com


Adjusting the crimping dimensions

The adjustment mechanism is used to set the crimping depth of the crimping mandrel as described below.

The adjusting dial is used to prepare the feed; the dial can be turned clockwise (for decreasing the dimension) or counter-clockwise (for increasing the dimension).

Adjustment precision

- 1 division mark on the dial v 1/100 mm adjustment
- 1 complete revolution of the dial v 0.2 mm adjustment read from scale
- 5 revolutions of the dial v 1 mm adjustment read from scale



Verifying the crimping dimension

The four-mandrel crimping tool is pre-set at the factory. The actual crimping size should still be checked periodically. It should be checked using the plug gauge (Ø 1.0 mm) that is included with the crimping tool as described below. Use the dial on the stationary tool shank to set the size to 1.0 mm on the scale. Set to the zero-point tick mark on the dial and close the tool. (Refer to the diagram showing the crimping size adjustment.) At this setting, it should be possible to move the 1.00-mm-Ø plug gauge without any play or extra room. If this is not possible, then the size deviation (+/-) can be determined using the dial's fine-adjustment mechanism. If this size check reveals that the tool is not within the tolerance range specified by the manufacturer of the contacts, then you should contact the manufacture of the tool for further inspection.

Servicing and maintenance

Before you start to use the hand crimping tool, it must be clean and in proper working condition. Crimp residue or fragments must be removed from the crimping jaws and locator. The joints should be regularly lubricated using machine oil to protect them from dirt. Make sure that all bolts are secured with locking rings.

Technical data

Crimp contact	Wire cross-section (mm ²)	Crimping mandrel adjustment	Locator position	Order No.			
Crimp male 1 mm	0.14	0.86	1	1170150000			
	0.25	0.90					
	0.34	0.95					
	0.56	0.98					
	0.75	1.03					
	1.00	1.08					
Crimp female 1 mm (0.08-0.56 mm ²)	0.08	0.75	2	1995860000			
	0.14	0.78					
	0.25	0.82					
	0.34	0.86					
	0.56	0.90					
	Crimp female 1 mm (0.34-1.00 mm ²)	0.34			0.77	2	1170180000
0.56		0.82					
0.75		0.88					
1.00		0.95					
Crimp male 1.5 mm		0.14	0.65	3	1170220000		
		0.25	0.68				
	0.34	0.72					
	0.56	0.81					
	0.75	0.95					
	1.00	1.07					
Crimp female 1.5 mm (0.14-0.75 mm ²)	0.14	0.70		1170230000			
	0.25	0.73					
	0.34	0.77					
	0.56	0.85					
	0.75	1.05					
	Crimp female 1.5 mm (0.34-1.00 mm ²)	0.34			0.88		1170240000
0.56		0.95					
0.75		1.05					
1.00		1.13					
Crimp male 2.0 mm		0.75	1.20		1170250000		
		1.00	1.35				
	1.50	1.45					
	2.50	1.60					
	Crimp female 2.0 mm	0.75	1.25				1170260000
		1.00	1.35				
1.50		1.45					
2.50		1.60					

Ordering data

Type	Order No.
SAI M23 CRIMPING TOOL 2	1203960000