


Metallscheibe

Standardklasse, Maß T frei wählbar/konfigurierbar



T-Maß frei wählbar (Standardklasse)

Teilenummer Ausführung	D	V Auswahl	T Auswahl	Stückpreis		
				WSSB	WSSM	WSSS
WSSB WSSM WSSS	4	2	1 2			
			1.5 2.5			
	5	2 3	1 2			
		3	1.5 2.5 3			
	6	2 3 4	1 2			
		3 4	1.5 2.5 3 4 5 6			
	8	2 3 4 5 6	1 2 3 5			
		3 4 5 6	1.5 2.5 4 6 8			
	10	2 3 4 5 6 8	1 2 3 5			
		3 4 5 6 8	1.5 2.5 4 6 8			
	12	3 4 5 6 8 10	1 2 3 5			
		4 5 6 8 10	1.5 2.5 4 6 8			
	13	4 5 6 8 10	1 2 3 5			
		5 6 8 10	1.5 2.5			
		6 8 10	4 6 8			
	14	4 5 6 8 10	1 2 3 5			
		5 6 8 10	1.5 2.5			
		6 8 10	4 6 8			
	15	4 5 6 8 10 12	1 2 3 5			
		5 6 8 10 12	1.5 2.5			
			4 6 8			
	16	4 5 6 8 10 12	1 2 3 5			
		6 8 10 12	1.5 2.5 4 6 8			
	20	4 5 6 8 10 12 15 16	1 2 3 5			
		6 8 10 12 15	1.5 2.5 4 6 8			
	25	6 8 10 12 15 16 20	1 2 3 5			
			4 6 8			
	30	8 10 12 15 16 20 25	1 2 3 5			
			4 6 8			
	35	10 12 15 16 20 25	3 5 10			
	40	10 12 15 16 20 25 30	3 5 10			
	50	10 12 15 16 20 25 30	3 5 10			
	60	15 16 20 25 30	3 5 10			

Ordering Example: Teilenummer - V - T
WSSS14 - 10 - 5

T-Maß konfigurierbar (Standardklasse)


Teilenummer Ausführung	D	V Auswahl	T 0.5mm- Schritte
TWSSB TWSSM TWSSS	4	2	1.0~10.0
	5	2 3	
	6	2 3 4	
	8	2 3 4 5 6	
	10	2 3 4 5 6 8	
	12	3 4 5 6 8 10	
	13	4 5 6 8 10	
	14	4 5 6 8 10	
	15	4 5 6 8 10 12	
	16	4 5 6 8 10 12	
	20	4 5 6 8 10 12 15 16	
	25	6 8 10 12 15 16 20	
	30	8 10 12 15 16 20 25	

Ordering Example: Teilenummer - V - T
TWSSB30 - 8 - 5.5

D	T	Stückpreis		
		TWSSB	TWSSM	TWSSS
4~10	1.0~ 2.0			
	2.5~ 5.0			
	5.5~10.0			
12~20	1.0~ 2.0			
	2.5~ 5.0			
	5.5~10.0			
25, 30	1.0~ 2.0			
	2.5~ 5.0			
	5.5~10.0			

Metallscheibe

Präzisionsklasse, Maß T frei wählbar/konfigurierbar



T-Maß frei wählbar (Präzisionsklasse)

Teilenummer Ausführung	D	V Auswahl	T Auswahl	Stückpreis		
				WASB	WASM	WASS
WASB WASM WASS	4	2	1 2			
	5	2 3	1 2			
	6	2 3 4	1 2			
		3 4	1.5			
	8	2 3 4 5 6	1 2 3 5			
		3 4 5 6	1.5			
	10	2 3 4 5 6 8	1 2 3 5			
		4 5 6 8	1.5 2.5			
	12	3 4 5 6 8 10	1 2 3 5			
		5 6 8 10	1.5 2.5			
	13	4 5 6 8 10	1 2 3 5			
		6 8	1.5 2.5			
	14	4 5 6 8 10	1 2 3 5			
		6 8 10	1.5			
	15	4 5 6 8 10 12	1 2 3 5			
		6 8 10 12	1.5			
	16	4 5 6 8 10 12	1 2 3 5			
		6 8 10 12	1.5			
	20	4 5 6 8 10 12 15 16	2 3 5			
		6 10 15	1.5 2.5			
	25	6 8 10 12 15 16 20	2 3 5			
	30	8 10 12 15 16 20 25	2 3 5			
	35	10 12 15 16 20 25	3 5 10			
	40	10 12 15 16 20 25 30	3 5 10			
	50	10 12 15 16 20 25 30	3 5 10			
	60	15 16 20 25 30	3 5 10			

Ordering Example: Teilenummer - V - T
WASB14 - 10 - 5

T-Maß konfigurierbar (Präzisionsklasse)

Teilenummer Ausführung	D	V Auswahl	T 0.5mm- Schritte
TWASB TWASM TWASS	4	2	1.0~10.0
	5	2 3	
	6	2 3 4	
	8	2 3 4 5 6	
	10	2 3 4 5 6 8	
	12	3 4 5 6 8 10	
	13	4 5 6 8 10	
	14	4 5 6 8 10	
	15	4 5 6 8 10 12	
	16	4 5 6 8 10 12	
	20	4 5 6 8 10 12 15 16	
	25	6 8 10 12 15 16 20	
	30	8 10 12 15 16 20 25	

Ordering Example: Teilenummer - V - T
TWASB30 - 8 - 5.5

D	T	Stückpreis		
		TWASB	TWASM	TWASS
4~10	1.0~ 2.0			
	2.5~ 5.0			
	5.5~10.0			
12~20	1.0~ 2.0			
	2.5~ 5.0			
	5.5~10.0			
25, 30	1.0~ 2.0			
	2.5~ 5.0			
	5.5~10.0			