

OIL-FREE THIN SLIDE PLATES

—COPPER ALLOY 5mm TYPE—

OIL-FREE SLIDE PLATE

—SKS3 (53~56HRC) 5mm TYPE—

ⓘ Non JIS material definition is listed on P.1351 - 1352

RoHS **UTW**

● 2-hole type

● 3-hole type

● 4-hole type

● 6-hole type

● Installation bolt

● Sliding direction

Loosening prevention treatment

ⓘ <What is Loosening Prevention Treatment?>
This treatment applies on the screw threads with a special plastic that excels in elasticity as well as abrasion and oil resistance. Its effect will gradually decrease from the 2nd use.

ⓘ Keep temperature under 80°C or lower.

■ Copper alloy
■ Special solid lubricant embedded
■ Flat Head Cap Screws

Bolt Hole Type	ℓ	ℓ ₁	Part Number	W	L	U/Price
						1~19
2 holes	20	—	UTW	28	50	Quotation
	45				75	
	70				100	
3 holes	60	—		38	50	
	45				75	
	70				100	
2 holes	20	—		48	75	
	45				100	
	95				125	
3 holes	60	45	75	100		
	95			125		
6 holes	60	70	100	150		
	70			100		
	95			125		
4 holes	70	70	100	100		
	95			125		
6 holes	60	70	100	150		
	60			150		

Order Part Number **UTW** W **75** — L **100**

ⓘ Prior to use, apply initial running-in grease for better performance.

Days to Ship **Quotation**

Price **Quotation**

RoHS **UTWSZ**

● Sliding direction

● Installation bolt

Loosening prevention treatment

ⓘ <What is Loosening Prevention Treatment?>
This treatment applies on the screw threads with a special plastic that excels in elasticity as well as abrasion and oil resistance. Its effect will gradually decrease from the 2nd use.

ⓘ Keep temperature under 80°C or lower.

■ SKS3
■ Special solid lubricant embedded
■ 53~56HRC
■ Flat Head Cap Screws

ℓ	Part Number	W	L	U/Price
				1~19
20	UTWSZ	28	50	Quotation
45			75	
70			100	
20		38	50	
45			75	
70			100	
45		48	75	
70			100	
70			100	

Order Part Number **UTWSZ** W **38** — L **100**

Price **Quotation**

Days to Ship **Quotation**

ⓘ Prior to use, apply initial running-in grease for better performance.