


STRIPPER PRESSURE PINS

STRIPPER PRESSURE PINS AND LIFTING COLLARS

RoHS



HSPP (Fixed P dimension type)
HSPPH (Configurable P dimension type)



SKS3
53 ~ 58HRC

H	Catalog No.		L	Base unit price 1 ~ 19 pieces
	Type	P		
20	HSPP	8	10.0 ~ 60.0	Quotation
22		10		
25		13		
27		16		
30		20		
35		25		

H	Catalog No.		L	Base unit price 1 ~ 19 pieces
	Type	No.		
10	HSPPH	10	10.0 ~ 60.0	Quotation
16		16		
20		20		
22		22		
25		25		
27		27		
30		30		
35		35		

Order

Catalog No.

L

P

HSPP 10

31.5

HSPPH 25

35.8

P16.5

Days to Ship

Quotation

Price

Quotation

Alterations

Catalog No.

L

P

(HC·TC)

HSPPH 25


35.8

P16.5

HC19~TC3

Alteration	Code	Spec.	1Code
	HC	Head diameter change (P+2) ≤ HC < H 0.1mm increments	Quotation
	TC	Head thickness change 2 ≤ TC < 5 0.1mm increments	


- Features
1. Excellent impact resistance due to the R of 0.5 - 1 under the head
 2. The head diameter is machined to match the coil spring diameter.
 3. Because the shaft diameter dimension (P) can be specified, these products can be used in small spaces. (HSPPH)



RoHS




PWP



SKS3
53 ~ 58HRC

H	Catalog No.		L	Base unit price 1 ~ 19 pieces
	Type	D		
13	PWP	8	15.0 ~ 70.0	Quotation
16		10		
21		13		
25		16		
30		20		



Order

Catalog No.

L

PWP 16

50.0

Days to Ship

Quotation

Price

Quotation

Alterations

Catalog No.

L

(HC·TC)

PWP 8

50.5


HC10~TC5

Alteration	Code	Spec.	1Code
	HC	Head diameter change D ≤ HC < H 0.1mm increments	Quotation
	TC	Head thickness change 2 ≤ TC < 7 0.1mm increments	


RoHS



SBKP (Pressure pin)



SBKT (Lifting collar)



If orders are placed in units of the quantity used for a single die (40 or less), they will all be ground at the same time.
In this way, although the L dimension tolerance is ±0.05, the variation in the finished L dimension will be 0.01 or less.


For SBKT, depending on the L dimension, the tap pilot hole may go all the way through.
When 4M > L, a through-tap is used. (SBKT only)

Equivalent to SKD11
53 ~ 58HRC


RoHS



SBKS (Pressure pin)



SBK (Lifting collar)



If orders are placed in units of the quantity used for a single die (40 or less), they will all be ground at the same time.
In this way, although the L dimension tolerance is ±0.05, the variation in the finished L dimension will be 0.01 or less.

For SBK, depending on the L dimension, the tap pilot hole may go all the way through.
When 2M > L, L is a through-tap. (SBK only)

SCM435
53 ~ 38HRC

M×P	Catalog No.		L	Base unit price 1~19 pieces
	Type	D		
5×0.8	SBKP SBKT	8	20.0 ~ 60.0	Quotation
		10		
6×1.0		13		
		16		
8×1.25		20		

Deq	F	ℓ	S	M×P	Catalog No.		L	Base unit price 1~19 pieces
					Type	D		
10	8	15	8	5×0.8	SBKS SBK	10	20.0 ~ 60.0	Quotation
13				6×1.0		13		
16				8×1.25		16		

Order

Catalog No.

L

SBKP 16

50.0

Days to Ship

Quotation

Price

Quotation

Alterations

Catalog No.

L

(LKC·SC)

SBKT 13

45.0

LKC


Alteration	Code	Spec.	1Code
	LKC	L dimension tolerance change L±0.05 ⇒ L ^{+0.02} ₀ If LKC is used, L dimension can be selected in 0.01mm increments.	Quotation
	SC	Machining of wrench flat. Can be used for SBKP and SBKT. Cannot be used for SBKT8.	

Washers for pressure pins and lifting collars

RoHS



SBW



S45C
48 ~ 52HRC

t	Catalog No.		d
	Type	D	
5	SBW	20	5
		22	5
		25	6
7		27	5
		30	6
		35	8

For delivery and prices P.816