



STROKE END BLOCKS

—FLAT TYPE—




CEBY (End block for plain guide post)
CEBA (End block for ball guide post)

M SS400
A 2 bolts

PD: Outside diameter of post



CSBY (Stock block for plain guide post)
CSBA (Stock block for ball guide post)



M SS400

PD	D	CEBY	CEBA	CSBY	CSBA	S	r2	Bolt	l
		D1	D1	r1	r1				
25	46	29	31.5	14.5	15.75	37	23	M4×P0.7	10
32	56	37	41	18.5	20.5	45	28	M4×P0.7	10
38	72	43	49	21.5	24.5	60	36	M5×P0.8	10
50	86	56	62	28	31	72	43	M6×P1.0	10
60	112	66	76	33	38	92	56	M8×P1.25	12
80	140	88	100	44	50	116	70	M8×P1.25	12

■ End blocks

Catalog No.	Type	PD	H1 5mm increments	Color	Base unit price	
					1~9 pieces	
CEBY		25	10~50	R (Red)		
		32	10~60			
CEBA		38	15~70	Y (Yellow)		
		50	20~80			
		60	20~80			
		80	20~80			

Order Catalog No. — H1 — Color (R·Y)
CEBY 32 — 35 — R

Days to Ship Quotation

Price Quotation

■ Stock blocks


Catalog No.	Type	PD	H2 5mm increments	Color	Base unit price	
					1~9 pieces	
CSBY		25	10~40	R (Red)		
		32	10~40			
CSBA		38	10~50	Y (Yellow)		
		50	10~50			
		60	10~50			
		80	10~50			

Order Catalog No. — H1 — Color (R·Y)

Days to Ship Quotation

Price Quotation

Example



Catalog No.	Type	PD	(1)~(2)(End block)		Color	(3)~(4)(Stock block)		Base unit price
			H1 5mm increments	H2 5mm increments		H1 5mm increments	H2 5mm increments	
EBYS		25	10~30		R (Red)	10~20	10~20	1~9 sets
		32	35~50			25~40	25~40	
		38	10~30			10~20	10~20	
		50	35~50			25~40	25~40	
		60	15~30			10~20	10~20	
EBAS		38	35~50		R (Red)	25~50	25~50	1~9 sets
		50	35~50			10~20	10~20	
		60	35~50			25~50	25~50	
		80	20~30			10~20	10~20	
		80	35~50			25~50	25~50	

This product was discontinued in 2017.

Catalog No. : EBYS EBAS


HOLDER GUIDE
POST SETS

Order Catalog No. — (1)~(2) — (3)~(4)	Type PD H1 Color(R·Y) H2 Color(R·Y)	Days to Ship Quotation
EBYS 38 — 40 R — 40 Y		

Alterations Catalog No. — H(1~2) — Color(R·Y) — (S-RS-HC-NMC)	Days to Ship Quotation
CSBY50 — 35 — R — RS CEBA60 — 40 — Y — HC32	

Alteration Code	Machining for chain attachment S	Machining for reinforced chain(RSC) attachment RS	H1 dimension change HC	Machining of groove NMC
Spec.			Lifting eye bolts M10×20 with nut	
			Tap hole processing on the end block for chain mounting. Tap hole processing on the stock block for chain mounting. Reinforced chain (RSC) is attached to stock block. Can be used for PD≥25, H1≥20, and H2≥20. The chain is attached to the stock block. Cannot be combined with alteration S. Cannot be used for CSBY and CSBA.	1 dimension change H1 min. < HC < H1 max. 1mm increments Please order according to the alteration order example. Cannot be used for CSBY and CSBA. Cannot be used for RSC3.

■ Chains for end blocks



Catalog No.	Base unit price
Type	1~9 pieces
RSC 3	
RSC 5	

This product, RSC3, is a chain for alteration RS.

Order Catalog No. RSC 3	Days to Ship Quotation
-------------------------	------------------------

Days to Ship Quotation	Price Quotation
------------------------	-----------------