

PRECISION CARBIDE BLOCK PUNCHES WITH AIR HOLES

		RoHS				•Tip machining limit		Tip shape		Tip shape		Tip shape	
						D		R		E			
						P ≥ W		P ≥ W		0.15 ≤ R < W/2		P > W	