


RIGID FLYING CAM UNITS

— MGFL · MEFL —

MGFL80 ($\theta=60-65$)
MEFL80 ($\theta=60-65$)

(Economy type)



Components table P.1287

W	θ	A	B	C	E	F	H	x
80	60	208.58	228.58	20	181.73	88.27	139.3	23
	65	203.67	233.67	30	191.87	78.13	140.8	

Slide Stroke S	Working force KN (tonf)		Spring load N (kgf)			Total weight kg	Catalog No.	W	θ
	Standard working force	Max. working force	Preload	5mm before bottom dead center	Max. load				
61.1	49.0 (5.0)	98.1 (10.0)	566 (57.7)	1805 (184.1)	1914 (195.2)	31.0	MGFL MEFL (Economy type)	80	60
70.9				1818 (185.4)					65

Order -
MGFL 80 - 60

Days to Ship **Quotation**

Price **Quotation**

Alterations - - (N12 · K · KA)
MGFL 80 - 60 - K

Alterations	Code	Spec.
	N12	Change dowel hole diameter $\phi 13H7 \Rightarrow \phi 12H7$
	K	Add 3 locating keys (With 3 hexagon socket head cap screws M8×15)
	KA	Add 3 stepped locating keys (With 3 hexagon socket head cap screws M8×15)